


CUSTOMER TERMINAL	RoHS	LEAD(Pb)-FREE
Sn96%, Ag4%	Yes	Yes



ELECTRICAL SPECIFICATIONS @ 25°C unless otherwise noted:

PARAMETER	TEST CONDITIONS	VALUE
D.C. RESISTANCE	1-4 tie(1+2, 3+4), @20°C	0.047 ohms ±20%
D.C. RESISTANCE	5-6 @20°C	0.100 ohms ±10%
D.C. RESISTANCE	7-12 tie(7+8+9, 10+11+12), @20°C	0.023 ohms ±20%
INDUCTANCE	1-4 tie(1+2, 3+4), 100kHz, 100mVAC, L _s	100uH ±15%
LEAKAGE INDUCTANCE	1-4 tie(1+2, 3+4, 5+6, 7+8+9+10+11+12), 100kHz, 100mVAC, L _s	0.5uH typ., 1.0uH max.
DIELECTRIC	1-7 tie(3+4+5, 10+11+12), 1875VAC, 1 second	1500VAC, 1 minute
DIELECTRIC	1-5 tie(3+4), 625VAC, 1 second	500VAC, 1 minute
TURNS RATIO	(1-4):(7-12), tie(1+2, 3+4, 7+8+9, 10+11+12)	1.33:1
TURNS RATIO	(1-4):(5-6), tie(1+2, 3+4)	1.6:1

GENERAL SPECIFICATIONS:

OPERATING TEMPERATURE RANGE: -40°C to +125°C including temp rise.

Safety standard undefined.

Wire insulation & RoHS status not affected by wire color.
Wire insulation color may vary depending on availability.

REV.	DATE	Packaging Specifications	CONVENTION PLACEMENT	Tolerances unless otherwise specified:	DRAWING TITLE	PART NO.
		Method: Tape & Reel PKG-0868 www.we-online.com/midcom		Angles: ±1° Fractions: ±1/64 Decimals: ±.005 [.13] Footprint: ±.005 [.13]	TRANSFORMER	750320145
6A	6/25	SEE REVISION SHEET FOR REVISION LEVEL		This drawing is dual dimensioned. Dimensions in brackets are in millimeters.	eiSos p/n: 750320145	SPECIFICATION SHEET 1 OF 1