

CUSTOMER TERMINAL	RoHS	LEAD(Pb)-FREE
Sn96%, Ag4%	Yes	Yes

more than you expect





ELECTRICAL SPECIFICATIONS @ 25°C unless otherwise noted:

PARAMETER	TEST CONDITIONS	VALUE
D.C. RESISTANCE	10-7 tie(10+11, 7+8), @20°C	0.116 ohms max.
INDUCTANCE	10-7 tie(10+11, 7+8), 10kHz, 100mVAC, Ls	40.00uH ±10%


GENERAL SPECIFICATIONS:

OPERATING TEMPERATURE RANGE: -40°C to +125°C including temp rise.

CURRENT RATING: 3.2A



10+11 are tubed.
Customer to tie terminals 7+8 and 10+11
on PC board for correct operation.



RECOMMENDED
P.C. PATTERN, COMPONENT SIDE

Wire insulation & RoHS status not affected by wire color.
Wire insulation color may vary depending on availability.

REV.	DATE	Packaging Specifications	Tolerances unless otherwise specified:	DRAWING TITLE	PART NO.
		Method: Tray	Angles: ±1°	INDUCTOR	750341495
		PKG-1175	Decimals: ±.005 [.13]		
		www.we-online.com/midcom	Fractions: ±1/64		
6A	12/21	SEE REVISION SHEET FOR REVISION LEVEL	This drawing is dual dimensioned. Dimensions in brackets are in millimeters.	eiSos p/n: 750341495	SPECIFICATION SHEET 1 OF 1