



CUSTOMER TERMINAL	RoHS	LEAD(Pb)--FREE
Sn 96%, Ag 4%	Yes	Yes

more than you expect




**ELECTRICAL SPECIFICATIONS @ 25° C unless otherwise noted:**

PARAMETER	TEST CONDITIONS	VALUE
D.C. RESISTANCE	S-F @20°C	0.060 ohms max.
INDUCTANCE	S-F 10kHz, 100mV, Ls	480µH ±15%
SATURATION CURRENT	S-F 25% rolloff from initial	15A



RECOMMENDED P.C. PATTERN, COMPONENT SIDE



**GENERAL SPECIFICATIONS:**

OPERATING TEMPERATURE RANGE: -40°C to +125°C including temp rise.

Rating current: 10A

Wire insulation & RoHS status not affected by wire color. Wire insulation color may vary depending on availability.

DFM	Packaging Specifications		Tolerances unless otherwise specified: Angles: ±1°      Decimals: ±.005 [.13] Fractions: ±1/64      Footprint: ±.005 [.13]	DRAWING TITLE  <b>INDUCTOR</b>	PART NO.  <b>750344413</b>
DATE	Method: Tray				
ENG	PKG-1123	This drawing is dual dimensioned. Dimensions in brackets are in millimeters.			SPECIFICATION SHEET 1 OF 1
REV.	00				
DATE	8/27/2019	<a href="http://www.we-online.com/midcom">www.we-online.com/midcom</a>			