



CUSTOMER TERMINAL	RoHS	LEAD(Pb)-FREE
Sn96%, Ag4%	Yes	Yes



ELECTRICAL SPECIFICATIONS @ 25°C unless otherwise noted:

PARAMETER	TEST CONDITIONS	VALUE
6B D.C. RESISTANCE 1-3	@20°C	0.46 ohms max.
6B D.C. RESISTANCE 6-4	@20°C	0.48 ohms max.
INDUCTANCE 1-3	10kHz, 100mVAC, L _s	1.0mH min.
6G INTERWINDING CAPACITANCE 1-6	100kHz, 10mVAC, C _s	12.5pF typ.
DIELECTRIC 1-6	1875VAC, 1 second	1500VAC, 1 minute
6H TURNS RATIO	(6-4):(1-3)	1.1:1



GENERAL SPECIFICATIONS:

6B OPERATING TEMPERATURE RANGE: -40°C to +125°C.

CURRENT RATING: 100mAAC

VOLTAGE-TIME: 7VuS


6D Qualified to AEC-Q200.

Wire insulation & RoHS status not affected by wire color.
Wire insulation color may vary depending on availability.

760390011S: 6H
Packaging Specifications
Method: Tape & Reel
PKG-1346
www.we-online.com/midcom

760390011:

REV.	DATE	Packaging Specifications	Tolerances unless otherwise specified:	DRAWING TITLE	PART NO.
6H	11/24	Method: Tape & Reel	Angles: ±1°	TRANSFORMER	760390011/S
6G	4/21	PKG-0895	Decimals: ±.005 [.13]		
6F	12/20	www.we-online.com/midcom	Fractions: ±1/64		
6E	7/16	SEE REVISION SHEET FOR REVISION LEVEL	Footprint: ±.005 [.13]		



CONVENTION PLACEMENT

This drawing is dual dimensioned. Dimensions in brackets are in millimeters.

eiSos p/n: 760390011, 760390011S



SPECIFICATION SHEET 1 OF 1