

**Maximum Input 36V / 0.5A / Fixed Output 12V**
**DESCRIPTION**

The FDSM series of the MagI<sup>3</sup>C Power Module family is a fixed output voltage, fully integrated DC-DC power supply including the controller IC, inductor and capacitors all in one package.

For optimal performance the module is recommended for use with external input and output capacitors as well as with an input filter.

The FDSM ensures fast time to market and low development costs.

The module is pin compatible with the common 78xx linear regulator series. The high efficiency reduces the power dissipation and in many cases a heatsink and assembly parts are unnecessary.



The standard THT (11.6 x 7.55 x 10.16mm) package allows for easy assembly.

**FEATURES**

- Peak efficiency up to 96%
- Current capability up to 0.5A
- Input voltage up to 36V
- No minimum load required
- Partially integrated input and output capacitors
- Integrated inductor
- Low output voltage ripple (<50mV<sub>pp</sub>)
- PFM/PWM mode
- Internal soft-start
- Thermal shutdown
- Short circuit protection
- Cycle by cycle current limit
- Pin compatible with the FDSM power modules series
- Ambient temperature range: -40°C to 85°C
- RoHS & REACH compliant
- Complies with EN 55032 (CISPR 32) class B conducted and radiated emissions standard

**TYPICAL APPLICATIONS**

- Point-of-Load DC-DC applications
- Replacement for linear regulators
- Interface and microcontroller supplies
- General purpose


**TYPICAL CIRCUIT DIAGRAM**


## CONTENTS

|           |                                                                         |           |
|-----------|-------------------------------------------------------------------------|-----------|
| <b>1</b>  | <b>PINOUT</b>                                                           | <b>4</b>  |
| <b>2</b>  | <b>ORDERING INFORMATION</b>                                             | <b>5</b>  |
| <b>3</b>  | <b>PINOUT COMPATIBLE FAMILY MEMBERS</b>                                 | <b>5</b>  |
| <b>4</b>  | <b>SALES INFORMATION</b>                                                | <b>5</b>  |
| <b>5</b>  | <b>ABSOLUTE MAXIMUM RATINGS</b>                                         | <b>6</b>  |
| <b>6</b>  | <b>OPERATING CONDITIONS</b>                                             | <b>6</b>  |
| <b>7</b>  | <b>ELECTRICAL SPECIFICATIONS</b>                                        | <b>7</b>  |
| <b>8</b>  | <b>RoHS, REACH</b>                                                      | <b>8</b>  |
| <b>9</b>  | <b>RELIABILITY</b>                                                      | <b>8</b>  |
| <b>10</b> | <b>PACKAGE SPECIFICATIONS</b>                                           | <b>8</b>  |
| <b>11</b> | <b>NOTES</b>                                                            | <b>8</b>  |
| <b>12</b> | <b>TYPICAL PERFORMANCE CURVES</b>                                       | <b>9</b>  |
| 12.1      | Radiated and Conducted Emissions EN 55032 (CISPR 32) Class B Compliance | 9         |
| 12.1.1    | Radiated Emissions EN 55032 (CISPR 32) Class B Compliant Test Setup     | 9         |
| 12.1.2    | Conducted Emissions EN 55032 (CISPR 32) Class B Compliant Test Setup    | 9         |
| 12.1.3    | Radiated and Conducted Emissions                                        | 10        |
| 12.2      | DC Performance Curves                                                   | 11        |
| 12.2.1    | Efficiency                                                              | 11        |
| 12.2.2    | Thermal Derating                                                        | 11        |
| 12.2.3    | Load Regulation                                                         | 12        |
| 12.2.4    | Line Regulation                                                         | 12        |
| <b>13</b> | <b>BLOCK DIAGRAM</b>                                                    | <b>13</b> |
| <b>14</b> | <b>CIRCUIT DESCRIPTION</b>                                              | <b>13</b> |
| <b>15</b> | <b>OUTPUT VOLTAGE RIPPLE</b>                                            | <b>14</b> |
| <b>16</b> | <b>PROTECTION FEATURES</b>                                              | <b>15</b> |
| 16.1      | Soft-Start                                                              | 15        |
| 16.2      | Over Temperature Protection (OTP)                                       | 15        |
| 16.3      | Short Circuit Protection (SCP)                                          | 16        |
| 16.4      | Over Current Protection (OCP)                                           | 16        |
| <b>17</b> | <b>DESIGN EXAMPLE</b>                                                   | <b>17</b> |
| 17.1      | Layout                                                                  | 17        |
| 17.2      | Schematic                                                               | 18        |
| 17.3      | Bill of Materials                                                       | 18        |
| <b>18</b> | <b>OUTPUT VOLTAGE FEATURES</b>                                          | <b>19</b> |
| 18.1      | Generating Negative Output Voltage                                      | 19        |
| 18.2      | Generating Complementary Output Voltage                                 | 20        |

|                                    |           |
|------------------------------------|-----------|
| <b>19 HANDLING RECOMMENDATIONS</b> | <b>21</b> |
| 19.1 Soldering Profile             | 21        |
| <b>20 PHYSICAL DIMENSIONS</b>      | <b>22</b> |
| 20.1 Component                     | 22        |
| 20.2 Recommended Drill Holes       | 23        |
| 20.3 Tube                          | 23        |
| <b>21 DOCUMENT HISTORY</b>         | <b>24</b> |
| <b>22 LIST OF FIGURES</b>          | <b>25</b> |
| <b>23 LIST OF TABLES</b>           | <b>26</b> |
| <b>24 CAUTIONS AND WARNINGS</b>    | <b>27</b> |
| <b>25 IMPORTANT NOTES</b>          | <b>28</b> |

1 PINOUT (PACKAGE TYPE F)




Figure 1: Pinout type F package (pins are located at the front).

Table 1: Marking description.

| MARKING   | DESCRIPTION                                        |
|-----------|----------------------------------------------------|
| WE        | Würth Elektronik eiSos GmbH & Co. KG               |
| 78        | Indicates compatibility with 78xx linear regulator |
| 173951236 | Order code                                         |
| YY        | Year                                               |
| WW        | Calendar week                                      |
| VV        | Output voltage                                     |

Table 2: Pin description.

| SYMBOL | NUMBER | TYPE  | DESCRIPTION                                                                                                                                   |
|--------|--------|-------|-----------------------------------------------------------------------------------------------------------------------------------------------|
| VIN    | 1      | Power | The supply input pin is a terminal for an input voltage source. It is recommended to use input capacitors connected between this pin and GND. |
| GND    | 2      | Power | Ground pin. Reference for VIN and VOUT.                                                                                                       |
| VOUT   | 3      | Power | Regulated output voltage pin. There is no need for an external output capacitor.                                                              |

## 2 ORDERING INFORMATION

| ORDER CODE | SPECIFICATIONS        | PACKAGE      | PACKAGING UNIT      |
|------------|-----------------------|--------------|---------------------|
| 173951236  | 36V / 0.5A / 12V Vout | SIP-3 Type F | Tube with 43 pieces |

## 3 PINOUT COMPATIBLE FAMILY MEMBERS

Table 3: Pinout compatible family members.

| ORDER CODE | SPECIFICATIONS           | PACKAGE      | PACKAGING UNIT      |                     |              |
|------------|--------------------------|--------------|---------------------|---------------------|--------------|
| 173950378  | 28V / 0.5A / 3.3V Vout   | SIP-3 Type F | Tube with 42 pieces |                     |              |
| 173950578  | 28V / 0.5A / 5V Vout     |              |                     |                     |              |
| 173010378  | 28V / 1A / 3.3V Vout     |              |                     |                     |              |
| 173010578  | 28V / 1A / 5V Vout       |              |                     |                     |              |
| 173010342  | 42V / 1A / 3.3V Vout     |              |                     |                     |              |
| 173010542  | 42V / 1A / 5V Vout       |              |                     |                     |              |
| 173950336  | 36V / 0.5A / 3.3V Vout   |              | SIP-3 Type F        | Tube with 43 pieces |              |
| 173950536  | 36V / 0.5A / 5V Vout     |              |                     |                     |              |
| 173951236  | 36V / 0.5A / 12V Vout    |              |                     |                     |              |
| 173951536  | 36V / 0.5A / 15V Vout    |              |                     |                     |              |
| 173010335  | 36V / 1A / 3.3V Vout     |              |                     |                     |              |
| 173010535  | 36V / 1A / 5V Vout       |              |                     |                     |              |
| 173011235  | 36V / 1A / 12V Vout      |              |                     |                     |              |
| 173011535  | 36V / 1A / 15V Vout      |              |                     |                     |              |
| 173020336  | 36V / 2A / 3.3V Vout     |              |                     |                     | SIP-3 Type B |
| 173020536  | 36V / 2A / 5V Vout       |              |                     |                     |              |
| 173021236  | 36V / 2A / 12V Vout      |              |                     |                     |              |
| 173950375  | 74.5V / 0.5A / 3.3V Vout |              |                     |                     |              |
| 173950575  | 74.5V / 0.5A / 5V Vout   |              |                     |                     |              |
| 173951275  | 74.5V / 0.5A / 12V Vout  |              |                     |                     |              |

## 4 SALES INFORMATION

Table 4: Sales information.

| SALES CONTACT                                                                                                                                                                                                                                                                                                                                                                                                                      |
|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| <p>Würth Elektronik eiSos GmbH &amp; Co. KG<br/>         EMC and Inductive Solutions<br/>         Max-Eyth-Str. 1<br/>         74638 Waldenburg<br/>         Germany<br/>         Tel. +49 (0) 7942 945 0<br/> <a href="http://www.we-online.com/powermodules">www.we-online.com/powermodules</a><br/>         Technical support: <a href="mailto:wpme-support@we-online.atlassian.de">wpme-support@we-online.atlassian.de</a></p> |

## 5 ABSOLUTE MAXIMUM RATINGS

### Caution:

Exceeding the listed absolute maximum ratings may affect the device negatively and may cause permanent damage.

Table 5: Absolute maximum ratings.

| SYMBOL               | PARAMETER                                                               | LIMIT              |                    | UNIT |
|----------------------|-------------------------------------------------------------------------|--------------------|--------------------|------|
|                      |                                                                         | MIN <sup>(1)</sup> | MAX <sup>(1)</sup> |      |
| V <sub>IN</sub>      | Input pin voltage                                                       | -0.3               | 45                 | V    |
| V <sub>OUT</sub>     | Output pin voltage                                                      | -0.3               | 25                 | V    |
| T <sub>storage</sub> | Assembled, non-operating storage temperature                            | -40                | 125                | °C   |
| V <sub>esd</sub>     | ESD Voltage (Human Body Model), according to EN61000-4-2 <sup>(4)</sup> | -4                 | 4                  | kV   |

## 6 OPERATING CONDITIONS

Operating conditions are conditions under which the device is intended to be functional. All values are referenced to GND.

MIN and MAX limits are valid for the recommended ambient temperature range of -40°C to 85°C. Typical values represent statistically the utmost probable values at the following conditions: V<sub>IN</sub> = 15V to 36V, I<sub>OUT</sub> = 0.5A, T<sub>A</sub> = 25°C, unless otherwise noted.

Table 6: Operating conditions.

| SYMBOL               | PARAMETER                             | MIN <sup>(1)</sup> | TYP <sup>(3)</sup> | MAX <sup>(1)</sup> | UNIT |
|----------------------|---------------------------------------|--------------------|--------------------|--------------------|------|
| V <sub>IN</sub>      | Input voltage                         | 15                 | -                  | 36                 | V    |
| T <sub>a</sub>       | Ambient temperature                   | -40                | -                  | 85 <sup>(2)</sup>  | °C   |
| I <sub>OUT</sub>     | Nominal output current <sup>(5)</sup> | -                  | -                  | 0.5                | A    |
| C <sub>OUT MAX</sub> | Maximum output capacitance            | -                  | -                  | 680                | µF   |

## 7 ELECTRICAL SPECIFICATIONS

### Caution:

MIN and MAX limits are valid for the recommended ambient temperature range of -40°C to 85°C. Typical values represent statistically the utmost probable values at the following conditions:  $V_{IN} = 24V$ ,  $V_{OUT} = 12V$ ,  $I_{OUT} = 0.5A$ ,  $T_A = 25^\circ C$ , unless otherwise noted.

Table 7: Electrical specifications.

| SYMBOL              | PARAMETER                       | TEST CONDITIONS                                  | LIMIT              |                    |                    | UNIT             |
|---------------------|---------------------------------|--------------------------------------------------|--------------------|--------------------|--------------------|------------------|
|                     |                                 |                                                  | MIN <sup>(1)</sup> | TYP <sup>(3)</sup> | MAX <sup>(1)</sup> |                  |
| Output Current      |                                 |                                                  |                    |                    |                    |                  |
| I <sub>CL</sub>     | Current limit threshold         |                                                  | —                  | 1.5                | —                  | A                |
| Output Voltage      |                                 |                                                  |                    |                    |                    |                  |
| V <sub>OUT</sub>    | Regulated output voltage        |                                                  | —                  | 12                 | —                  | V                |
|                     | Line regulation                 |                                                  | -0.4               | ±0.2               | 0.4                | %                |
|                     | Load Regulation                 | 10% to 100% load                                 | —                  | ±0.3               | —                  | %                |
|                     | Total output voltage regulation |                                                  | -4                 | ±2                 | 4                  | %                |
|                     | Output voltage ripple           |                                                  | —                  | 30                 | —                  | mV <sub>pp</sub> |
| Switching Frequency |                                 |                                                  |                    |                    |                    |                  |
| f <sub>SW</sub>     | Switching frequency             |                                                  | —                  | 710                | —                  | kHz              |
| Input Current       |                                 |                                                  |                    |                    |                    |                  |
| I <sub>IN</sub>     | No load input current           | Operating, switching                             | —                  | 0.1                | 1                  | mA               |
| Efficiency          |                                 |                                                  |                    |                    |                    |                  |
| η                   | Efficiency                      |                                                  | —                  | 94                 | —                  | %                |
|                     |                                 | V <sub>IN</sub> = 15V, I <sub>OUT</sub> = 0.225A | —                  | 96                 | —                  | %                |

## 8 RoHS, REACH

Table 8: RoHS, REACH.

|                 |                                                                                   |                                                                                                                                                                                         |
|-----------------|-----------------------------------------------------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| RoHS directive  |  | Directive 2011/65/EU of the European Parliament and the Council of June 8th, 2011 on the restriction of the use of certain hazardous substances in electrical and electronic equipment. |
| REACH directive |                                                                                   | Directive 1907/2006/EU of the European Parliament and the Council of June 1st, 2007 regarding the Registration, Evaluation, Authorization and Restriction of Chemicals (REACH).         |

## 9 RELIABILITY

Table 9: Reliability.

| SYMBOL | PARAMETER                  | TEST CONDITIONS      | TYP <sup>(3)</sup>     | UNIT |
|--------|----------------------------|----------------------|------------------------|------|
| MTBF   | Mean time between failures | MIL-HDBK-217F, 25 °C | 2000 · 10 <sup>3</sup> | h    |

## 10 PACKAGE SPECIFICATIONS

Table 10: Package specifications.

| ITEM             | PARAMETER                                                   | TYP <sup>(3)</sup>      | UNIT |
|------------------|-------------------------------------------------------------|-------------------------|------|
| Case             | Black flame-retardant and heat-resistant plastic (UL94 V-0) | -                       | -    |
| Potting material | Polyurethane (UL94 V-0)                                     | -                       | -    |
| Weight           |                                                             | 1.8                     | g    |
| Vibration        | 5g for 20 min                                               | MIL-STD-202, Method 204 |      |

## 11 NOTES

- (1) Min and Max limits are 100% production tested at 25 °C. Limits over the operating temperature range are guaranteed through correlation using Statistical Quality Control (SQC) methods.
- (2) Measured without heatsink. Natural convection (0 - 20LFM / 0- 0.1m/s) on a 57 x 35mm two layer test board, with 35µm (1 ounce) copper.
- (3) Typical numbers are valid at 25 °C ambient temperature and represent statistically the utmost probable values assuming a Gaussian distribution.
- (4) The human body model is a 100pF capacitor discharged through a 1.5kΩ resistor into each pin. Test method is per JESD-22-114.
- (5) Depending on ambient temperature; see [THERMAL DERATING](#).



## 12 TYPICAL PERFORMANCE CURVES

If not otherwise specified, the following conditions apply:  $V_{IN} = 24V$ ;  $V_{OUT} = 12V$ ;  $I_{OUT} = 0.5A$ ;  $T_{AMB} = 25^{\circ}C$ .

### 12.1 Radiated and Conducted Emissions EN 55032 (CISPR 32) Class B Compliance

The 173951236 power module is tested with a standard EMC configuration (1m wire between the module and the load) to give more realistic information about implementation in the applications. The test setup is based on CISPR 16 with the limit values taken from CISPR 32.

Measured with module on the design example shown in chapter [DESIGN EXAMPLE](#) in a Fully Anechoic Room (FAR) at 3m antenna distance.

#### 12.1.1 Radiated Emissions EN 55032 (CISPR 32) Class B Compliant Test Setup

- Measured in a Fully Anechoic Room (FAR) at 3m antenna distance
- Input wire length: 160cm (80cm horizontal + 80cm vertical)
- Output wire length: 1m

#### 12.1.2 Conducted Emissions EN 55032 (CISPR 32) Class B Compliant Test Setup

- Measurement input wire length: 80cm
- Output wire length: 1m

### 12.1.3 Radiated and Conducted Emissions




Figure 2: Radiated EMI with input filter.




Figure 3: Conducted EMI with input filter.

## 12.2 DC PERFORMANCE CURVES

### 12.2.1 EFFICIENCY




Figure 4: Efficiency.

### 12.2.2 THERMAL DERATING




Figure 5: Thermal derating.

### 12.2.3 LOAD REGULATION




Figure 6: Load regulation.

### 12.2.4 LINE REGULATION




Figure 7: Line regulation.

### 13 BLOCK DIAGRAM




Figure 8: Block diagram.

### 14 CIRCUIT DESCRIPTION

The MagI<sup>3</sup>C power module 173951236 is based on an asynchronous step-down regulator with integrated IC, free-wheeling diode, power inductor, input and output capacitors. The control scheme is based on a current mode (CM) regulation loop.

The  $V_{OUT}$  of the regulator is divided by the internal feedback resistor network and fed into the error amplifier, which compares this signal with the internal 0.75V reference. The error amplifier controls the on-time of a fixed frequency pulse width generator, which drives the MOSFET.

This architecture supports fast transient response and very small output voltage ripple values (<30mV<sub>pp</sub>) are achieved.

## 15 OUTPUT VOLTAGE RIPPLE

The output voltage ripple depends on several parameters. The figure below shows the  $V_{OUT}$  ripple at full load using no external output capacitor. An output voltage ripple of less than  $30\text{mV}_{pp}$  is measured under the conditions indicated. To reduce the output ripple further it is recommended to follow the [DESIGN EXAMPLE](#).




Figure 9: Output voltage ripple,  $V_{IN} = 24\text{V}$ ,  $I_{OUT} = 0.5\text{A}$ .

## 16 PROTECTION FEATURES

### 16.1 Soft-Start

An internal soft-start of approximately 1.5ms prevents the output voltage from overshooting during start up.




Figure 10: Soft-start.

### 16.2 Over Temperature Protection (OTP)

Thermal protection helps to prevent catastrophic failures due to accidental device overheating. The junction temperature of the MagI<sup>3</sup>C power module should not be allowed to exceed its maximum ratings. Thermal protection is implemented by an internal thermal shutdown circuit which activates at 170°C (typ.), causing the device to enter a low power standby state. In this state, the MOSFET remains off, causing  $V_{OUT}$  to fall. When the junction temperature falls back below 160°C (typ.) (hysteresis is implemented)  $V_{OUT}$  rises smoothly and normal operation resumes.

### 16.3 Short Circuit Protection (SCP)

The short circuit protection is realized via cycle by cycle current monitoring and comparison of the switch current to an internal reference. If the output voltage is pulled low by external factors, the switch current will be driven to the switch current limit. Normal operation will resume when the output short circuit condition is removed.




Figure 11: Short circuit protection.

### 16.4 Over Current Protection (OCP)

For protection against load faults, the power module incorporates cycle by cycle current monitoring. Every cycle the switch current is compared to an internal reference. When the peak transistor current meets the reference value, the switch is turned off. This limits the output current during an over current scenario. Normal operation will resume when the over current condition is removed.




Figure 12: Over current protection.



## 17 DESIGN EXAMPLE

The design example shows a possible solution for 24V to 12V with a max lout of 0.5A. All of the necessary components to fulfill the requirements of the CISPR-32 EMI conducted and radiated emissions tests are included in the design example. It passes the conducted emissions class B with 0.8m input and 1m output lines and passes the radiated emissions class B in a FAR at 3m measurement distance with 0.8m horizontal, 0.8m vertical input and 1m horizontal output lines. Filter components may be omitted depending on the requirements of the final application.

### 17.1 Layout




Figure 13: Layout recommendation.

The layout above has been evaluated to provide the optimal performance in terms of transient response, efficiency, ripple and EMI. The design footprint can be reduced at the expense of performance in these parameters.

The following recommendation should be followed when designing the layout:

1. The input and output capacitors should be placed as close as possible to the module pins.
2. The bulk capacitor should be placed close to the input capacitors of the module.
3. To avoid direct coupling of the DC-DC converter's E- and H-fields into connectors, filter components and cables, the module must be placed as far away from these components as possible.

## 17.2 Schematic




Figure 14: Design example schematic.

## 17.3 Bill of Materials

Table 11: Design example bill of materials.

| DESIGNATOR | DESCRIPTION                                                                     | FUNCTION      | QUANTITY | ORDER CODE   | MANUFACTURER |
|------------|---------------------------------------------------------------------------------|---------------|----------|--------------|--------------|
| FDSM       | Magl <sup>3</sup> C power module                                                | Power supply  | 1        | 173951236    | WE           |
| LF         | Filter inductor, 1μH, PD2 family, I <sub>SAT</sub> = 5.72A, I <sub>R</sub> = 4A | Input Filter  | 1        | 7447730      | WE           |
| CF         | Ceramic chip capacitor 4.7μF, 50V, X7R, 1210                                    | Input Filter  | 2        | 885012209048 | WE           |
| CIN        | Ceramic chip capacitor 4.7μF, 50V, X7R, 1210                                    | Input Filter  | 2        | 885012209048 | WE           |
| COUT       | Ceramic chip capacitor 22μF/25V, X5R, 1210                                      | Output Filter | 2        | 885012109014 | WE           |

## 18 OUTPUT VOLTAGE FEATURES

### 18.1 Generating Negative Output Voltage

Many industrial applications require negative voltages. The 173951236 can easily provide a negative voltage using the circuit shown below. The module's VOUT pin is attached to the application ground and the module's GND pin is used to provide the output voltage. For low output voltage ripple, it is recommended to follow the external component recommendations given in the [DESIGN EXAMPLE](#).




Figure 15: Negative output voltage.

For additional information, please refer to the Application Note [ANS007b](#).

#### Operating Conditions for Generating Negative Output Voltage:

| Part Number | Minimum $V_{in}$ (V) | Maximum $V_{in}$ (V) | Maximum $I_{out}$ (-mA) | Maximum $C_{out}$ ( $\mu$ F) |
|-------------|----------------------|----------------------|-------------------------|------------------------------|
| 173951236   | 8                    | 24                   | 150                     | 330                          |

## 18.2 Generating Complementary Output Voltage

Another common requirement in industrial applications is to provide a complementary voltage (e.g.  $\pm 12\text{V}$ ). The circuit below shows how this target can be achieved simply combining one of the 173951236 family used in a standard configuration (delivering a positive output voltage) with the above mentioned solution for negative voltages. For low output voltage ripple, it is recommended to follow the external component recommendations given in the [DESIGN EXAMPLE](#).




Figure 16: Complementary output voltage.

## 19 HANDLING RECOMMENDATIONS

1. According to JEDEC J-STD033 an MSL classification is not applicable for THT components. Therefore the power module does not require special handling or storage to protect it from ambient moisture.
2. The profile below is valid for wave soldering only.

### 19.1 Soldering Profile

Table 12: Wave solder profile.

| Profile Feature                    | Old standard (Pb)             | New (Pb-free)                 |
|------------------------------------|-------------------------------|-------------------------------|
| Time within peak temperature $t_p$ | max. 10s<br>max. 5s each wave | max. 10s<br>max. 5s each wave |
| Average ramp-up rate               | 200°C/s                       | 200°C/s                       |
| Final preheat temperature $T_s$    | 130°C/s                       | 130°C/s                       |
| Peak temperature $T_p$             | +235°C/s                      | +260°C/s                      |
| Ramp-down rate                     | -5°C/s                        | -5°C/s                        |
| Heating rate during preheat        | 4°C/s                         | 4°C/s                         |

#### Wave Solder Diagram:




Figure 17: Solder profile.

#### Manual Soldering

1. Maximum soldering temperature should not exceed  $365^{\circ}\text{C} \pm 15^{\circ}\text{C}$ .
2. Maximum soldering time: max. 3 seconds.

## 20 PHYSICAL DIMENSIONS

### 20.1 Component




Figure 18: Physical dimensions.

## 20.2 Recommended Drill Holes




Figure 19: Recommended drill holes.

## 20.3 Tube




Figure 20: Tube.

Table 13: Packaging dimensions.

| Dimension | L     | W      | H     |
|-----------|-------|--------|-------|
| Tolerance | typ.  | typ.   | typ.  |
| Value     | 528mm | 16.9mm | 9.6mm |

## 21 DOCUMENT HISTORY

Table 14: Document history.

| Revision | Date           | Description                                  | Comment                                                                                                                                                                                                                                                                 |
|----------|----------------|----------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| 1.0      | May 2019       | Initial data sheet release                   |                                                                                                                                                                                                                                                                         |
| 2.0      | September 2021 | Added 173951236 and 173951536 family members |                                                                                                                                                                                                                                                                         |
| 3.0      | May 2022       | PCN                                          | 1. Corrected absolute maximum table parameters description for Vesd. (page 5)<br>2. Updated front page drawing. (page 1)<br>3. Updated pinout drawing to include pin 1 marking. (page 2)<br>4. Updated physical dimensions drawings to include pin 1 marking. (page 38) |
| 4.0      | June 2025      | PCN Major Change                             | Due to an improvement of the production capability, Würth Elektronik eiSos has shifted the production of the affected order codes to a new factory location.                                                                                                            |



## 22 LIST OF FIGURES

|    |                                                                    |    |
|----|--------------------------------------------------------------------|----|
| 1  | Pinout. . . . .                                                    | 4  |
| 2  | Radiated EMI with input filter. . . . .                            | 10 |
| 3  | Conducted EMI with input filter. . . . .                           | 10 |
| 4  | Efficiency. . . . .                                                | 11 |
| 5  | Thermal derating. . . . .                                          | 11 |
| 6  | Load regulation. . . . .                                           | 12 |
| 7  | Line regulation. . . . .                                           | 12 |
| 8  | Block diagram. . . . .                                             | 13 |
| 9  | Output voltage ripple, $V_{IN} = 24V$ , $I_{OUT} = 0.5A$ . . . . . | 14 |
| 10 | Soft-start. . . . .                                                | 15 |
| 11 | Short circuit protection. . . . .                                  | 16 |
| 12 | Over current protection. . . . .                                   | 16 |
| 13 | Layout recommendation. . . . .                                     | 17 |
| 14 | Design example schematic. . . . .                                  | 18 |
| 15 | Negative output voltage. . . . .                                   | 19 |
| 16 | Complementary output voltage. . . . .                              | 20 |
| 17 | Solder profile. . . . .                                            | 21 |
| 18 | Physical dimensions. . . . .                                       | 22 |
| 19 | Recommended drill holes. . . . .                                   | 23 |
| 20 | Tube. . . . .                                                      | 23 |

23 LIST OF TABLES

|    |                                           |    |
|----|-------------------------------------------|----|
| 1  | Marking description. . . . .              | 4  |
| 2  | Pin description. . . . .                  | 4  |
| 3  | Pinout compatible family members. . . . . | 5  |
| 4  | Sales information. . . . .                | 5  |
| 5  | Absolute maximum ratings. . . . .         | 6  |
| 6  | Operating conditions. . . . .             | 6  |
| 7  | Electrical specifications. . . . .        | 7  |
| 8  | RoHS, REACH. . . . .                      | 8  |
| 9  | Reliability. . . . .                      | 8  |
| 10 | Package specifications. . . . .           | 8  |
| 11 | Design example bill of materials. . . . . | 18 |
| 12 | Wave solder profile. . . . .              | 21 |
| 13 | Packaging dimensions. . . . .             | 23 |
| 14 | Document history. . . . .                 | 24 |

## 24 CAUTIONS AND WARNINGS

The following conditions apply to all goods within the product series of MagI<sup>3</sup>C of Würth Elektronik eiSos GmbH & Co. KG:

### General:

- All recommendations according to the general technical specifications of the data-sheet have to be complied with.
- The usage and operation of the product within ambient conditions which probably alloy or harm the component surface has to be avoided.
- The responsibility for the applicability of customer specific products and use in a particular customer design is always within the authority of the customer. All technical specifications for standard products do also apply for customer specific products
- Residual washing varnish agent that is used during the production to clean the application might change the characteristics of the body, pins or termination. The washing varnish agent could have a negative effect on the long term function of the product. Direct mechanical impact to the product shall be prevented as the material of the body, pins or termination could flake or in the worst case it could break. As these devices are sensitive to electrostatic discharge customer shall follow proper IC Handling Procedures.
- Customer acknowledges and agrees that it is solely responsible for compliance with all legal, regulatory and safety-related requirements concerning its products, and any use of Würth Elektronik eiSos GmbH & Co. KG components in its applications, notwithstanding any applications-related information or support that may be provided by Würth Elektronik eiSos GmbH & Co. KG.
- Customer represents and agrees that it has all the necessary expertise to create and implement safeguards which anticipate dangerous consequences of failures, monitor failures and their consequences lessen the likelihood of failures that might cause harm and take appropriate remedial actions
- Customer will fully indemnify Würth Elektronik eiSos and its representatives against any damages arising out of the use of any Würth Elektronik eiSos GmbH & Co. KG components in safety-critical applications

### Product specific:

Follow all instructions mentioned in the datasheet, especially:

- The solder profile has to comply with the technical reflow or wave soldering specification, otherwise this will void the warranty.
- All products are supposed to be used before the end of the period of 12 months based on the product date-code.
- Violation of the technical product specifications such as exceeding the absolute maximum ratings will void the warranty.
- It is also recommended to return the body to the original moisture proof bag and reseal the moisture proof bag again.
- ESD prevention methods need to be followed for manual handling and processing by machinery.

### Disclaimer:

This electronic component has been designed and developed for usage in general electronic equipment only. This product is not authorized for use in equipment where a higher safety standard and reliability standard is especially required or where a failure of the product is reasonably expected to cause severe personal injury or death, unless the parties have executed an agreement specifically governing such use. Moreover Würth Elektronik eiSos GmbH & Co. KG products are neither designed nor intended for use in areas such as military, aerospace, aviation, nuclear control, submarine, transportation (automotive control, train control, ship control), transportation signal, disaster prevention, medical, public information network etc. Würth Elektronik eiSos GmbH & Co. KG must be informed about the intent of such usage before the design-in stage. In addition, sufficient reliability evaluation checks for safety must be performed on every electronic component which is used in electrical circuits that require high safety and reliability functions or performance. These cautions and warnings comply with the state of the scientific and technical knowledge and are believed to be accurate and reliable. However, no responsibility is assumed for inaccuracies or incompleteness.

## 25 IMPORTANT NOTES

### General Customer Responsibility

Some goods within the product range of Würth Elektronik eiSos GmbH & Co. KG contain statements regarding general suitability for certain application areas. These statements about suitability are based on our knowledge and experience of typical requirements concerning the areas, serve as general guidance and cannot be estimated as binding statements about the suitability for a customer application. The responsibility for the applicability and use in a particular customer design is always solely within the authority of the customer. Due to this fact it is up to the customer to evaluate, where appropriate to investigate and decide whether the device with the specific product characteristics described in the product specification is valid and suitable for the respective customer application or not. Accordingly, the customer is cautioned to verify that the datasheet is current before placing orders.

### Customer Responsibility Related to Specific, in Particular Safety-Relevant, Applications

It has to be clearly pointed out that the possibility of a malfunction of electronic components or failure before the end of the usual lifetime cannot be completely eliminated in the current state of the art, even if the products are operated within the range of the specifications. In certain customer applications requiring a very high level of safety and especially in customer applications in which the malfunction or failure of an electronic component could endanger human life or health it must be ensured by most advanced technological aid of suitable design of the customer application that no injury or damage is caused to third parties in the event of malfunction or failure of an electronic component.

### Best Care and Attention

Any product-specific notes, warnings and cautions must be strictly observed. Any disregard will result in the loss of warranty.

### Customer Support for Product Specifications

Some products within the product range may contain substances which are subject to restrictions in certain jurisdictions in order to serve specific technical requirements. Necessary information is available on request. In this case the field sales engineer or the internal sales person in charge should be contacted who will be happy to support in this matter.

### Product R&D

Due to constant product improvement product specifications may change from time to time. As a standard reporting procedure of the Product Change Notification (PCN) according to the JEDEC-Standard we inform about minor and major changes. In case of further queries regarding the PCN, the field sales engineer or the internal sales person in charge should be contacted. The basic responsibility of the customer as per Section 1 and 2 remains unaffected.

### Product Life Cycle

Due to technical progress and economical evaluation we also reserve the right to discontinue production and delivery of products. As a standard reporting procedure of the Product Termination Notification (PTN) according to the JEDEC Standard we will inform at an early stage about inevitable product discontinuance. According to this we cannot guarantee that all products within our product range will always be available. Therefore it needs to be verified with the field sales engineer or the internal sales person in charge about the current product availability expectancy before or when the product for application design-in disposal is considered. The approach named above does not apply in the case of individual agreements deviating from the foregoing for customer-specific products.

### Property Rights

All the rights for contractual products produced by Würth Elektronik eiSos GmbH & Co. KG on the basis of ideas, development contracts as well as models or templates that are subject to copyright, patent or commercial protection supplied to the customer will remain with Würth Elektronik eiSos GmbH & Co. KG. Würth Elektronik eiSos GmbH & Co. KG does not warrant or represent that any license, either expressed or implied, is granted under any patent right, copyright, mask work right, or other intellectual property right relating to any combination, application, or process in which Würth Elektronik eiSos GmbH & Co. KG components or services are used.

### General Terms and Conditions

Unless otherwise agreed in individual contracts, all orders are subject to the current version of the "General Terms and Conditions of Würth Elektronik eiSos Group", last version available at [www.we-online.com](http://www.we-online.com).